
KEMET Part Number: SSR10H-08220

(UALR10H0822000)



KEMET, SSR10V/H, AC Line Filters, Common Mode, 0.022 H



Dimensions		
L	22mm MAX	
Т	18mm MAX	
Н	13.5mm MAX	
LL	3.5mm +/-0.5mm	
S	17mm +/-0.5mm	

Packaging Specifications		
Packaging:	Tray	
Packaging Quantity:	300	
Weight:	9 g	

General Information		
Series:	SSR10V/H	
Style:	Through-Hole	
Features:	Small Standard Common Mode, High Permeability, Compact Size, Low Profile, Light Weight, High Impedance, Strong Inductance	
RoHS:	Yes	
Miscellaneous:	55 (K) Temperature Rise Max.	

Specifications		
Voltage AC:	250 VAC	
Inductance:	22 mH (10 kHz)	
Current:	800 mA	
Temperature Range:	-25/+120°C	
DC Resistance:	650 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

