

# STORA

2370PJP125S74

EAN 4031582428438

Swivel castor, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, wheel axle with nut, threaded stem with square neck, riveted. Wheel centre made of Polypropylene, Tread: TENTEpren (thermoplastic rubber), grey non-marking, precision ball bearing, with threadguards



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	125 mm
Wheel width	32 mm
Threaded stem	M12X15,5 mm
Offset	38 mm
Swivel Interference	201 mm
Overall height	154 mm
Temperature	- 20 / + 60 °C
Standard	EN_12530
Swivel Radius	100.5 mm
Hardness of tread	Shore A 85
Load capacity	100 kg
Load capacity (static)	200 kg

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○