

# Rittal – The System.

Faster – better – everywhere.

## Compact system enclosures CM – CM 5114.500

Date : Nov 15, 2016

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Compact system enclosures CM – CM 5114.500

created: 15.11.2016 build on [www.rittal.com/th-en](http://www.rittal.com/th-en)



## Product description

|  |  |
|--|--|
| <b>Material:</b>                                 | Enclosure: Sheet steel 1.5 mm<br>Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Sheet steel 3.0 mm            |
| <b>Surface finish:</b>                           | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                          |
| <b>Colour:</b>                                   | RAL 7035   |
| <b>Protection category<br/>IP to IEC 60 529:</b> | IP 55 with selection of the appropriate gland plates or trim panel   |
| <b>Protection category<br/>NEMA:</b>             | NEMA 12 with selection of the appropriate gland plates or trim panel   |
| <b>IK Code:</b>                                  | IK08   |
| <b>Supply includes:</b>                          | Enclosure with hinged door(s)<br>3-point locking system with double-bit insert<br>Mounting plate<br>Open base for individual cable entry |
| <b>Basic material:</b>                           | Sheet steel  |

## Product features

|                        |   |
|------------------------|---|
| <b>Dimensions:</b>     | Width: 800 mm<br>Height: 1000 mm<br>Depth: 300 mm |
| <b>Mounting plate:</b> | Width: 740 mm                                     |

Height: 955 mm

|  |               |
|--|---------------|
| <b>Number of doors:</b>                                      | 1             |
| <b>Door hinged on the right, may be swapped to the left:</b> | yes           |
| <b>Packs of:</b>   | 1 pc(s).      |
| <b>Weight/pack:</b>  | 57 kg         |
| <b>EAN:</b>  | 4028177479739 |
| <b>Customs tariff number:</b>                                | 94032080      |
| <b>ETIM 6.0:</b>   | EC000261      |
| <b>ETIM 5.0:</b>   | EC000261      |
| <b>eCl@ss 8.0/8.1:</b>                                       | 27180101      |
| <b>eCl@ss 7.0/7.1:</b>                                       | 27180101      |
| <b>eCl@ss 6.0/6.1:</b>                                       | 27180101      |
| <b>eCl@ss 5.1/5.1.4:</b>                                     | 27180102      |

## Approvals

|                      |   |
|----------------------|---|
| <b>Approvals:</b>    | CSA<br>Lloyds Register of Shipping<br>TÜV<br>UL + C-UL  |
| <b>Certificates:</b> | IK-Code   |
| <b>Declarations:</b> | Declaration of conformity<br>Manufacturer's declaration |