

**FatMax®**



MaxSteel® Heavy Duty Bench Vice

- ➔ Cast iron construction for strength and durability
- ➔ Base bolts directly to work bench surface for stability
- ➔ Base swivels and locks for versatility
- ➔ Roll-formed screw threads ensure smooth operation and durability
- ➔ Chrome-plated to resist corrosion

| <b>STANLEY</b>             | <u>83-066</u> | <u>83-067</u> | <u>83-068</u> |
|----------------------------|---------------|---------------|---------------|
| Weight in g                | 13000         | 18000         | 27000         |
| Throat Depth (mm)          | 85            | 95            | 105           |
| Clamping Capacity (mm)     | 100           | 125           | 150           |
| Clamping Capacity (inches) | 4             | 5             | 6             |
| Clamping force (kg)        | 1400          | 1800          | 2200          |