

Circular Saw LXT®

DSS501

18V • 3 600 min⁻¹ • 136 mm

Efficient and compact professional saw

A small and efficient cordless circular saw for wood. Accepts blades with 136 mm diameter that achieve a max. cutting depth of 51 mm. Ventilation air is guided through the front to keep the cut line clear and an LED light offers added illumination.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Max. Cutting Depth at 90°	51 mm
Max. Cutting Depth at 45°	35 mm
Max. Cutting Depth at 50°	30 mm
No load speed	3600 min ⁻¹
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,4 - 2,7 kg
Product Dimensions (L x W x H):	364 x 183 x 201 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Bevel Range (Right)	0 - 50 °
Blade Diameter	136 mm

User benefits

- Compact and lightweight design
- LED light illuminates the work site
- The rubber coating on the handle ensures a firm working grip
- Removable dust extraction connection
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.dk



Related products

Optional AC

164095-8 Parallel Guide		194415-2 Dust Nozzle Ø 25 / 31 Mm	
783203-8 Hex Wrench 5 Mm		821551-8 Makpac case (3)	
837628-9 MakPac (3) Inlay		B-33532 Circular Saw Blade, Specialized,	
B-33629 Circular Saw Blade, Specialized		B-33635 Circular Saw Blade, Specialized	

Other

User manual

Parts drawing