

uvexSAFETY
EYEWEAR25.06.2015
SBU-E-PGM-PM**Product Datasheet model carbonvision 9307 375****UVEX ARBEITSSCHUTZ GMBH, Würzburger Str. 181-189,
D-90766 Fürth**

Product characteristics	<ul style="list-style-type: none">* The world's lightest wide-vision goggles* Flexible soft components adapt perfectly to your face shape and ensure a perfect fit* Outstanding seal and splashproof protection* High-quality, long-lasting headband* Combinable with disposable respirators and bump caps
Technical details	
Frame	Front piece
Material	PP
Colour	black
Layer	
Material	TPU
Colour	grey

Manufacturer's ID code	Marking W
Applicable EN norm	166
Field of use	3 (drops and splashes of liquid) 4 (large dust particles)
Impact resistance	B (120 m/s)
Conformity symbol	CE
Material	Headband synthetic
Features	Convenient clip to remove headband before cleaning
Colour	grey/black
Lens	
Material	PC
Thickness	2,1 mm
Coating	supravision extreme
Colour	clear
Filter	Marking 2-1,2 (DIN EN 170)
Manufacturer's ID code	W
Optical class	1
Impact resistance	B (120 m/s)
Surface resistance to fine particles	K
Antifog	N
Tested acc. to DIN	DIN
Conformity symbol	CE
Miscellaneous	
Weight	46 g
Packing	5 goggles per box 160 pieces in one carton
Standards	DIN EN 166 + DIN EN 170