

Datasheet

RS Pro Stainless Steel Abrasive Circular Brush, 18000rpm, 40mm Diameter

RS Stock No: **779-289**



Product Details

RS Pro stainless steel abrasive circular brush has a diameter of 40 mm with a shaft diameter of 6 mm. A circular wire brush is used in power tools. It is perfect for cleaning welds or removing burr from steel enclosures or fittings.

Features and Benefits

- Suitable for cleaning or finishing hard to reach areas or internal surfaces
- 18000 rpm maximum safe speed
- Stainless steel bristle construction
- Shank fixing type



ENGLISH

Specifications:

Bristle Material	Stainless Steel
Fixing Type	Shank
Bristle Length	10 mm
Diameter	40 mm
Fixing Size	6 mm
Maximum Safe Speed	18000 rpm
Suitable For	Cleaning or Finishing Hard to Reach Areas or Internal Surfaces