

PREVOST FILTRATION - UNIT COMBINATIONS

Filter-regulator-lubricator - 2 units



Part number	Female thread	Pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Temperature min/ max (°C)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU B2585100	G1/8	6.00	400.00	5.00 / 50.00	10.00	25.00	0,687
ATU B2585101	G1/4	6.00	700.00	5.00 / 50.00	10.00	25.00	0,687
ATU B2585102	G3/8	6.00	2000.00	5.00 / 50.00	10.00	25.00	2,073
ATU B2585103	G1/2	6.00	3300.00	5.00 / 50.00	10.00	25.00	2,073

