

General Information

Extended Product Type:	R121/25
Product ID:	1SAR111025R4606
EAN:	4013614340345
Catalog Description:	R121/25 Solid-state relay A1-A2=4-32VDC, 42-530VAC, 25A
Long Description:	Solid-state relay R121/25, single-phase, width 44.8mm, A1-A2=4,5-32VDC, output 42-530VAC/25A, 1 n/o

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Solid State Relays

Ordering

EAN:	4013614340345
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85362010

Dimensions

Product Net Width:	44.8 mm
Product Net Height:	58.2 mm
Product Net Depth:	28.8 mm
Product Net Weight:	0.066 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	65 mm
Package Level 1 Height:	35 mm
Package Level 1 Length:	50 mm
Package Level 1 Gross Weight:	0.076 kg

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Additional Information

Function:	Solid-state relay
IIT Publishing Status:	Level 0 - Information enabled
Output:	1 n/o solid-state
Output Signal:	42-530 V AC / 25 A
Product Main Type:	R121
Product Name:	Solid-state relay
Rated Control Supply Voltage (U _s):	4 ... 32 V DC
Rated Operational Current AC-1 (I _a):	55 °C 25.0 A
RoHS Date:	0367
Sub-Function:	Single-phase

Certificates and Declarations (Document Number)

CSA Certificate:	CSA_213757
cUR Certificate:	cUR_E171990
Data Sheet, Technical Information:	2CDC110004C0203_07
Declaration of Conformity - CE:	1SAD938502-0017
RoHS Information:	1SAA981044-4401
UR Certificate:	UR_E171990

Classifications

eClass:	7.0 27371014
ETIM 4.0:	EC002055 - Solid state relay
ETIM 5.0:	EC002055 - Solid state relay
Object Classification Code:	Q
UNSPSC:	39121500

