



UC308D1

Set Screw Type

Included products

Bearing	UC308D1	Bearing
---------	---------	---------

Nominal Dimensions

d	40	mm	Bore diameter
D	90	mm	Outside diameter
B,B4	52	mm	Width of inner ring
C	27	mm	Outer ring width
r(min.)	2	mm	Chamfer dimension
S1	33	mm	Distance from locking device side face to raceway centre
G	10	mm	Distance face to thread centre
ds	M10×1.25		Set screw
Ca	6.1	mm	Distance from oil hole centre to raceway centre
d4	56	mm	Outside diameter of inner ring

Basic Load Ratings

Cr	40.5	kN	Basic dynamic load rating
C0r	24	kN	Basic static load rating

Mass

Mass approx.	0.96	kg	Mass approx.
--------------	------	----	--------------

