

ZCKE629

limit switch head ZCKE - steel roller plunger
with protective boot



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJD37 ZCKJ41 ZCKJ7 ZCKJ11H7 ZCKJ9H7 ZCKJD37H29 ZCKJD31H29 ZCKJ2 ZCKJD39 ZCKJ1 ZCKJ41H7 ZCKJ21H7 ZCKJD39H29 ZCKJ2H29 ZCKJ11 ZCKJD35 ZCKJ8H29 ZCKJ21 ZCKJ7H7 ZCKJD39H7 ZCKJ9H29 ZCKJ6H7 ZCKJ5H29 ZCKJ1H29 ZCKJ4H7 ZCKJ2H7 ZCKJD31H7 ZCKJ5 ZCKJ5H7 ZCKJ1H7 ZCKJ41H29 ZCKJ6H29 ZCKJ7H29 ZCKJD37H7 ZCKJ11H29 ZCKJD35H7 ZCKJ8H7 ZCKJ9 ZCKJ6 ZCKJD31 ZCKJ8 ZCKJ4 ZCKJ4H29 ZCKJD35H29 ZCKJ21H29
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal (with protective boot)
Type of approach	Lateral approach, 2 directions

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Package 1 Weight	152 g
Package 2 Weight	7.751 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------