

**PASE40-XL-N-FA125** [↗](#)

Plummer block housing unit

Plummer block housing units PASE...-FA125, cast iron housing, radial insert ball bearing with eccentric locking collar, P seals, with anti-corrosion protection

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps
Manufacturing instruction	FA125	Unit with Corrotect coating, corrosion-resistant

Main Dimensions & Performance Data

d	40 mm	Bore diameter
L	179 mm	Length total
H ₂	99 mm	Height
≈m	1.84 kg	Weight

Mounting dimensions

J	138.25 mm	Distance fixing bore
N	14 mm	Width (slot)
N ₁	26 mm	Length (slot)



Dimensions

H	49.2 mm	Distance shaft axis
A	48 mm	Width (base)
A ₁	30 mm	Width (head)
H ₁	19 mm	Heigth (base)
B ₁	43.8 mm	Locking collar total width
S ₁	32.8 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE08-FA125	Housing
GRAE40-XL-NPP-B-FA125	Bearing designation
KASK08	Protecting cap

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.