

Datasheet

ENGLISH

DC Axial Fan, 92.5 x 92.5 x 25mm, 74.8m/h, 2.9W, 24 V dc (OD9225 Series)

RS Stock number 541-5328



Frame and Impeller
PBT, UL94V-0 Thermoplastic

Available Options
Tachometer
Locked Rotor Alarm

Finger Guard: G92-16 Plastic Guard: G92P

Wire Mesh Guard: WMG92M Filter Kit: GRM92-30, GRM92-45

RS Part Number	Orion Part Number	Speed (RPM)	Airflow (CFM)	Noise (db)	Volts (DC)	Voltage Range	Current (Amps)	Lead Type
5415081		2900	52	31	12	7.0~13.6	0.25	Wire
5415075		2500	43	25	12	7.0~13.6	0.17	Wire
5415069	-	2000	36	22	12	7.0~13.6	0.13	Wire
5415334	_	2900	52	31	24	10~27	0.15	Wire
5415328	-	2500	43	25	24	10~27	0.12	Wire
5415312	-	2000	36	22	24	10~27	0.08	Wire

Data Tolerance +/- 10%


RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



onally approved products.

Datasheet

ENGLISH



*Drawing for Dimensional Reference Only

MOTOR

Brushless DC, polarity protected, locked rotor protected (current limited), auto restart

INSULATION RESISTANCE

Min. 10 M Ohm at 500VDC

LIFE EXPECTANCY (L10)

Ball Bearing 60,000 Hours

Operating Temperature

-10C ~ +70C

Safety Approvals

UL/CUL, TUV, CE