

## Features

- Material: High impact, warp-proof PVC , self-extinguishing .
- UL approved 94V-0.
- Color: Black
- Maximum service temperature: 85°C
- Test to UL up to 50°C.
- Supplied complete with cover.
- These devices are for routing of wires within devices in factory installations.
- Features parallel holes on both sidewalls to facilitate cutting in wire application.
- Easy to insert, adding or removing wires - even with terminations attached.
- Save your total cost for during installation, wire tracing and circuit troubleshooting.

## RS PRO Slotted Panel Trunking - Closed Slot, W 25 mm x D 30 mm, 2 m, Black

RS Stock No.: 301-2084, 301-2090, 301-2107, 301-2113, 301-2129, 301-2135



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- *Keep your workplace looking tidy and organized with RS PRO cable closed slot trunking. Simply clip the trunking onto any wall, desk or skirting for hassle-free cable access without the danger of accidental disconnection or tripping.*

## Mechanical Specifications

| RS Article No | W(mm) | H(mm) | A    | Slot | Length |
|---------------|-------|-------|------|------|--------|
| 301-2084      | 25    | 30    | 10   | 8MM  | 2M     |
| 301-2090      | 25    | 60    | 10   |      |        |
| 301-2107      | 40    | 40    | 17.5 |      |        |
| 301-2113      | 40    | 60    | 17.5 |      |        |
| 301-2129      | 50    | 50    | 22.5 |      |        |
| 301-2135      | 60    | 60    | 27.5 |      |        |

