



### Main

Range	Merten
Product or component type	Push-button
Device application	Lighting
Device presentation	Mechanism with fixing frame
Technology type	Electromechanical
Device mounting	Flush
Number of rocker	1
Actuator	Rocker

### Complementary

Contacts type and composition	1 NO
Local signalling	LED
Signalling function	Indicator
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 A
Connections - terminals	Screwless terminals
Fixing mode	By screws and claws

### Environment

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins