

FEATURES

- **Polyacrylic material:** Offers excellent chemical resistance and durability
- **Maximum operating pressure of 2000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 200 °C:** Performs well in high-temperature environments
- **Rotary speed of 10 m/s:** Ensures efficient sealing in dynamic applications
- **8 mm section:** Fits standard gland and valve sizes

RS PRO 8mm Gland Packing, Polyacrylic Material

RS Stock No: 606-582



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from durable polyacrylic material, it provides reliable sealing performance under high pressure and temperature conditions. Ideal for use in pumps and valves, it ensures efficient operation and longevity.

General Specifications

Maximum Operating Pressure	2000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	10 m/s
Section	8 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polyacrylic

Operation Environment Specifications

Maximum Operating Temperature	200 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------