

Main

| | |
|---------------------------|-----------------------------|
| Range | Odace |
| Product or component type | Reading lamp |
| Device application | Reading USB charger |
| Device mounting | Flush |
| Device presentation | Mechanism with fixing frame |
| Switch function | Dimmer |
| Switch application | On/off switching |
| Colour tint | White |
| Market segment | Hotel |

Complementary

| | |
|--------------------------------|---|
| Type of USB power supply | USB type A |
| Actuator | Push-button |
| Rated lamp wattage | 2 W |
| [Ue] rated operational voltage | 240 V |
| Bulb base | Integral LED |
| Bulb type | LED |
| Control type | Touch type |
| Luminous flux | 100 lm |
| Integrated connection type | USB port |
| Output current | 2.1 A |
| Fixing mode | Screws |
| Shape of screw head | Pozidriv No 1 |
| Clamping connection capacity | 2.5 mm ² for flexible cable(s) 2.5 mm ² for rigid cable(s) |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 45 mm |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant with Exemptions |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |