




Part Number : [1041270620](#)

Product Description : IllumiMate 1.00mm Pitch
Wire-to-Board Header, Surface Mount, Single Row,
Vertical, Side Lock, 6 Circuits

Series Number : 104127

Status : Obsolete

Product Category : PCB Headers and Receptacles



Documents & Resources


Specifications

[PK-104127-004-001.pdf](#)

[PS-104127-004-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	104127
Description	IllumiMate 1.00mm Pitch Wire-to-Board Header, Surface Mount, Single Row, Vertical, Side Lock, 6 Circuits
Application	Wire-to-Board
Component Type	PCB Header
Product Name	IllumiMate
UPC	889056135429

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer

Net Weight	0.201/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Retention	Yes
Pitch - Mating Interface	1.00mm
Plating min - Mating	3.000µm
Plating min - Termination	3.000µm
Temperature Range - Operating	-25° to +130°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
IllumiMate 1.00mm Pitch Wire-to-Board Crimp Housing, Single Row, Side Lock, 6 Circuits, Natural	<u>1041280610</u>