


## DALI PCU | Light management systems



### Areas of application

- Conference rooms
- Restaurants
- Shop lighting

### Product family benefits

- Intuitive manual dimming and switching
- Integrated DALI supply
- Individual setting of minimal brightness level

### Product family features

- Up to four DALI PCU can be connected in parallel to set up multiple control points
- Automatic synchronization between the control points
- Combinable with standard presence- and motion detectors with mains contact
- Behavior after power failure configurable
- Length of the DALI control cable: up to 300 m


## Product datasheet

### Technical data

#### Electrical data

Nominal voltage	230 V
Mains frequency	50...60 Hz
System wattage	2.00 W

#### Dimensions & weight



Length	48.0 mm
Width	49.0 mm
Height	22.0 mm
Product weight	36.00 g

#### Colors & materials

Product color	Light grey
---------------	------------

#### Temperatures & operating conditions

Ambient temperature range	0...+40 °C
---------------------------	------------

#### Capabilities

Dimmable	Yes
Dimming interface	DALI
Number of control outputs	1
Type of installation	Integrated in flush device box

#### Certificates & standards

Type of protection	IP20
Protection class	II
Approval marks – approval	VDE / CE

## Product datasheet

### Logistical data

Commodity code	853650809900
----------------	--------------

### Equipment / Accessories

- Suitable for up to 25 electronic control gears
- Flexible expansion via DALI repeaters or further DALI PCUs

### Download Data

File	
	User instruction DALI PCU
	User instruction DALI PCU
	User instruction DALI PCU
	User instruction 723913_Mounting instruction DALI PCU
	Declarations of conformity EU Declaration of Conformity 2019 9C1-3406454-EN-01
	Product movie 729387_How to install DALI PCU (EN)

### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899955622		Shipping carton box 60	344 mm x 254 mm x 278 mm	24.29 dm <sup>3</sup>	3607.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

### Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.