

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance.
- **Flanged Design:** Facilitates easy installation and secure positioning.
- **Dynamic Load Rating of 14 N/mm²:** Ensures reliable performance under dynamic conditions.
- **Static Load Rating of 50 N/mm²:** Supports high static loads for robust applications.
- **ISO 9001:2008 Certified:** Guarantees quality and consistency in manufacturing.

RS PRO 9.02 mm Plain Bearing, Flanged

RS Stock No: 528-033



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO plain bearing is designed for applications requiring reliable and efficient performance. Made from sintered bronze, it offers excellent durability and resistance to wear. Ideal for use in various industrial settings, this bearing ensures smooth operation and long service life.

General Specifications

Bore Size	9.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	14.04 mm
Width	14.13 mm

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

