

COMBINATION WRENCHES - METRIC | E113207

Description

- ISO 691 - ISO 1711-1 - ISO 3318 - ISO 7738 - DIN 3113
- 12-point OGV® ring angled at 15°.
- Open end angled at 15° from handle axis.
- OGV® profile maximizing the contact surface with the nut for a longer lifetime.
- Forged in Chrome Vanadium steel.
- High chrome finish.

Information

EAN	3258951132074
------------	---------------

A [mm]	12
---------------	----

B [mm]	27.5
---------------	------

B1 [mm]	19
----------------	----

C [mm]	4.8
---------------	-----

C1 [mm]	7
----------------	---

L [mm]	160
---------------	-----

Conditioning	1
---------------------	---

[g]	60
------------	----

