

BCC M334-0000-20-000-31X450-000

Order Code: BCC06Z7















| _ | | | |
|----|-----|------|------|
| Ba | SIC | feat | ures |

| Approval/Conformity |
|---------------------|
|---------------------|

CE cULus EAC WEEE

Electrical connection

Cable diameter D

3.5...5 mm Connection M8x1-Male, Straight, 4-pin, A-

Number of connectable contacts

System

coded

Can be fabricated

Electrical data

Operating voltage Ub 60 VDC / 60 VAC 4.0 A

Rated current (40 °C)

Environmental conditions

Ambient temperature

IP rating

-40...85 °C IP67

Material

Material grip

Subject to change without notice: PV159588

Material contact carrier Material contacts

Material cover nut

PA Brass Brass PBT

Mechanical data

Connection cross-section Tightening torque pigtail Type of wire mounting

0.14...0.5 mm² 0.4 Nm

Screw terminals

Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



PIN 1-4 usable