

## Features

- Ratchet crimping tool
- Ring Terminals  
6mm to 150mm
- Splice Connectors  
6mm to 70mm

## RS PRO Ratchet Crimper

RS Stock No.: 241-4710



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Heavy duty ratchet crimping tool for RS PRO terminals. The product is designed for RS PRO Uninsulated Tubular Ring Terminals 6mm to 150mm & RS PRO butt wire splice connectors 6mm to 70mm.

- Copper tube terminal
- Hexagonal crimp
- Simple crimping and release mechanism

## General Specifications

Crimp Tool Type	Crimp Tool Frame
For Use With	RS PRO Terminals
Ratcheting	Yes

## Mechanical Specifications

Overall Length	440 mm
Wire Size (mm <sup>2</sup> )	6 to 150 mm <sup>2</sup>
Wire Size (AWG)	10/11, 7, 5, 3, 2, 1/0, 2/0, 3/0, 4/0, 300
Crimping Force	55KN
Rated Operating Pressure	Approx 60 KN
Life span, cycles	10,000 +
Weight	2.45kg
Crimp nest	Max 120 mm <sup>2</sup>
Handle spread (closed)	130 mm/5.12 inch
Handle spread (open)	458 mm/18.03 inch
Handle opening angle	125°
Maximum handle force	Approx 25kg
Standard Die Length	30mm
Standard Die width	30mm
Standard Die Height	12mm
Maximum contact diameter	4mm

## Terminals

Uninsulated Tubular Ring Terminals	Butt Wire Splice Connectors
<a href="#">119-160</a>	<a href="#">119-182</a>
<a href="#">119-176</a>	<a href="#">119-198</a>
<a href="#">531-015</a>	<a href="#">119-211</a>
<a href="#">531-021</a>	<a href="#">119-277</a>
<a href="#">531-037</a>	<a href="#">119-233</a>
<a href="#">531-043</a>	<a href="#">119-249</a>
<a href="#">531-059</a>	
<a href="#">531-065</a>	
<a href="#">531-071</a>	
<a href="#">531-087</a>	
<a href="#">241-4631</a>	
<a href="#">531-885</a>	
<a href="#">531-891</a>	
<a href="#">531-908</a>	
<a href="#">531-914</a>	
<a href="#">531-920</a>	
<a href="#">241-4647</a>	
<a href="#">241-4669</a>	
<a href="#">241-4653</a>	
<a href="#">241-4675</a>	
<a href="#">241-4681</a>	
<a href="#">241-4704</a>	