


HC-B 6-AML

Order No.: 1771134



HEAVYCON panel mounting base B6, with single locking latch, height 27 mm, with flat gasket

Commercial data

GTIN (EAN)	 4 017918 035877
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 572 (PC-2011)

Product notes

WEEE/RoHS-compliant since:
06/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B6, BB10, DD24, M
Design	B6
Height	27 mm
Width	43 mm
Length	80 mm

Housing type	Panel mounting base, straight
Locking type	With single locking latch
Pg screw connection	None
Degree of protection for housing	IP65 protection when the connector is inserted
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	High-grade steel, handle: PA-GF
Material grip body interlock	PA-GF
Length of the assembly cutout	52 mm
Width of the assembly cutout	35 mm

Certificates / Approvals




Certification


GOST

Diagrams/Drawings

Dimensioned drawing



Dimensional drawing



Panel cutout