



DD081SPMS



Surge Device Spec:
Uc - 275V
In - 10kA
Imax - 20kA
Up - ≤1.2kV
Green (ok) Red (replace) status indicator

8 Way 100A Switch + SPD

General	Technical
<p>Box quantity: 1</p> <p>ABC indicator: A</p> <p>Colour: White</p>	<p>Associated standards: BS EN 61439-3</p> <p>Rated voltage: 220-250V</p> <p>Rated current: 100A</p> <p>Frequency: 50-60Hz</p> <p>Wiring system: 2 channel</p> <p>Ambient operating temperature: -5 to 40°C (24hour average not exceeding 25°C)</p> <p>Width in number of modular spacings: 12</p> <p>Nature of supply: AC</p> <p>DIN-rail: Yes</p> <p>Extension possible: Yes</p> <p>With lock: Optional</p> <p>Type of cover: Hinged</p> <p>Material housing: steel</p> <p>Plate thickness cabinet: 1.2mm</p> <p>Plate thickness door/cover: 1.2mm</p> <p>Mounting method: Surface</p>

Number of outgoing ways: 8

Copyright © 2017 Contactum Limited, Victoria House, 2 Blackmoor Lane, Croxley Green Business Park,
Watford, WD18 8GA

Source URL: <https://www.contactum.co.uk/content/dd081spms>