

# NORTON

SAINT-GOBAIN

Reshaping  
your  
world.



## R222 - Handy Rolls

### Handy Rolls Norton-R222-25x25m#40

Artical Number: 63642531849

EAN: 3157620352143



#### Description

R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal and finishing metal.

#### Features & Benefits

J-weight cloth backing

Premium aluminium oxide abrasive

Dispenser unit

#### Application Data

Material Application: NON-FERROUS  
Machine: Manual application  
Process: Sanding

Equipments:



#### Technical Data

MarketingCAP:	R222	Length:	
BackingMaterial:	Light Cotton J	Width:	25 mm
Grit:	40		
Color:	Maroon		
CoatedShape:	Rolls Trimmed		
CoatedSubShape:	Handyroll		
		Shape:	

#### Logistic Data

Naked Product Weight:	0.091 kg	Packed Product Dimension:	250 mm x 800 mm x 30 mm
Naked Product Dimension:	25x25m	pack Qty (parts per pack):	1 pc
Units per part:	1 pc	Packed Product Weight:	0.035 kg