


PXM7012/32S/CR Datasheet

Product Name // Front Panel Mount Connector PXM7012
Series 32 Contact Socket Crimp/Solder Termination
(contacts available separately) Metal Body

 [View Product Page](#)



// Product Description:

- Front Panel Mount Connectors
- Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
- Quick turn locking ring with less than quarter turn locking and positive feedback
- Plug or Socket
- 2, 3, 6, 10, 32 Contact with leading Earth contact on 3 Contact versions
- Screw, Crimp/Solder terminations available, depending on part code; Screw contacts supplied fitted, Crimp/Solder contacts and fitting tools available separately
- Choice of body material depending on part code:
- Plastic body (part codes prefixed PXP). PXP7082 (plastic) and PXM7082 (metal) Sealing Caps available separately to maintain IP rating of unmated connectors
- Metal body (part codes prefixed PXM). PXM7083 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with PXP7010/PXM7010 Series Flex Connectors

// General Information:

Product Display Title:	Front Panel Mount Connectors
Product Family:	Circular Power Connectors
Product Series:	7000 Series Buccaneer
Approvals:	cUL, UL
Body Material:	Zinc Alloy - Nickel Plated
Body Material Type:	Metal Body
Contact Type:	Socket Contact
Coupling Type:	Bayonet Lock
Current Max:	2A, 3A
Diameter Over Coupling Ring Mm:	42mm
Flamability Rating:	UL94V-0
Function:	Front Panel Mount Connector
Ip Rating:	IP66, IP68, IP69K
Max Contact Accomodation Awg:	26AWG
Min Contact Accomodation Awg:	22AWG
Max Contact Accomodation Mm2:	0.33mm2
Min Contact Accomodation Mm2:	0.13mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	32 Contacts
Voltage Max:	600V

// Product PDF Links

-  [7000 Series power connectors...](#)
-  [7000 Series metal body power...](#)

// Product 3D CAD Model Links

-  [PXM7012/32S/CR3D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)