

# Product data sheet

Specifications

## Repacked, Cover frame, Odace Styl, 3 gangs, white



S520706W



This repacked option saves 0.213 over the standard condition

### Main

|                           |                     |
|---------------------------|---------------------|
| Range                     | Odace               |
| Product or component type | Cover frame         |
| Aesthetic name            | Styl                |
| Installation direction    | Horizontal/vertical |
| Distance between centers  | 71 mm               |
| Colour tint               | White (RAL 9003)    |
| Type of packing           | Flow-pack           |
| Type of frame             | Triple              |
| Number of gangs           | 3 gangs             |

### Complementary

|                               |                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device mounting               | Flush                                                                                                                                                                                                                                                                                                                               |
| fixing mode                   | Clip-in                                                                                                                                                                                                                                                                                                                             |
| Surface finish                | Glossy                                                                                                                                                                                                                                                                                                                              |
| Material                      | Thermoplastic ABS-UV stabilised: decorative frame                                                                                                                                                                                                                                                                                   |
| Height                        | 85 mm                                                                                                                                                                                                                                                                                                                               |
| Width                         | 227 mm                                                                                                                                                                                                                                                                                                                              |
| Depth                         | 10 mm                                                                                                                                                                                                                                                                                                                               |
| Product weight                | 0.02999 kg                                                                                                                                                                                                                                                                                                                          |
| IK degree of protection       | IK04                                                                                                                                                                                                                                                                                                                                |
| IP degree of protection       | IP21D                                                                                                                                                                                                                                                                                                                               |
| resistance to chemical agents | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

### Environment

|                                     |                                                |
|-------------------------------------|------------------------------------------------|
| Ambient air temperature for storage | -5...50 °C                                     |
| Product certifications              | AENOR: 030/2205<br>LCIE: NF 603415A<br>N<br>NF |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                                                           |
|---------------------------------------|-----------------------------------------------------------|
| Ambient air temperature for operation | 5...45 °C                                                 |
| Standards                             | NF C 61-314<br>EN 60669-1<br>2006/95/EEC<br>UNE 20315-1-1 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1.000 cm  |
| Package 1 Width              | 8.600 cm  |
| Package 1 Length             | 23.000 cm |
| Package 1 Weight             | 32.000 g  |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 50        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 1.904 kg  |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

0.2 kg CO2 eq.

## Use Better



### Materials and Substances

SCIP Number

59bc1733-7007-4ba6-bfd5-f7904c7d9a13

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No