

FEATURES

- Abrasive grit "antislip" tapes
- Additional grip underfoot on smooth surfaces
- Ideal for indicating hazardous areas or safe escape routes
- Hard wearing and easy to install
- Available in a range of grades, lengths and widths
- Long lasting colour
- Self-adhesive backing

RS PRO Black 18.3m Hazard Tape, 152mm x

RS Stock No.: 762-1519



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Hazard Tapes & Barrier Tapes



Product Description

Anti-Slip tapes are designed to provide an extra comfort, confidence and safety on floor surfaces in hazardous areas such as warehouses, factories, stairs or even boats. They are ideal for use in any environment where slipping is a higher risk.

General Specifications

Colour	Black
Backing Material	Polyethylene
Installation Method	Pressure sensitive self-adhesive tape
Application	Suitable for stairs, ladders, ramps, walkways, vehicles and boats

Mechanical Specifications

Width	152mm
Length	183mm
Thickness	0.05mm
Tensile Strength	MD: 4.2 kg/15mm, CD: 3.1 kg/15mm
Elongation at Break	200±25%
Adhesive Material	Acrylic
Surface finish	Grit
Grit Size	46grit
Rolling Ball Tack	20cm
Shear Resistance	24hrs(1"X1"@1 kg)
Coating Thickness	0.05mm
Solvent Residual	>0.5%
Adhesion	2.5kg/1"
Release Force	13g/m^2
Dry Coating Weight	37g/m^2



Operation Environment Specifications

Minimum Operating Temperature	10°C
Environmental Resistance	Suitable for an indoor and outdoor environment
UV Resistance	Yes
Safe Temperature Range	-10°c to +60°c
Operation Temperature	10°c +

Approvals

A 11 /A 110 11	
Compliance/Certifications	EN13552



