


Shock absorber DYSD-Q11-32-25-Y1F-S-Y9

Part number: 8161535

FESTO



 General operating condition

Data sheet

Feature	Value
Size	32
Stroke	25 mm
Cushioning	Self-adjusting
Mounting position	optional
Position detection	Without
Symbol	00991495
Max. impact speed	1 m/s
Reset time at room temperature	0.3 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Cushioning length	25 mm
Max. stop force	6000 N
Max. energy consumption per stroke	220 J
Max. energy consumption per hour	180000 J
Max. residual energy	2 J
Reset force	150 N
Min. insertion force	480 N
Product weight	1050 g
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Galvanised steel
Material piston rod	High-alloy steel
Material nut	Galvanised steel