

**Table 7.25: Accessories for QOU Low Ampere Circuit Breakers (Except as Noted)**

Description	Order Qty.	Cat. No.	Unit \$ Price
Factory-installed ring tongue terminal, 10–32 screw, for 1P, 2P, 3P QOU, 10–60 A	—	Suffix -5283	
Hex drive 5/32 in. wire binding screw for QOU	—	Suffix -5280	
For padlocking 1P low ampere QOU circuit breaker in OFF or ON position	—	QOU1PA	
For padlocking 2P and 3P low ampere QOU circuit breaker in OFF or ON position	—	QOU1PL	
For padlocking 1P low ampere QOU circuit breaker in OFF position only	—	QOU1PAFLA♦	
For padlocking 2P and 3P low ampere QOU circuit breaker in OFF position only	—	QOU2PAFLA♦	
For padlocking 2P and 3P high ampere QOU circuit breaker in OFF position only	—	Suffix -7100	
Handle lock-out, ON or OFF position	—	HLO1♦	
4P 100 A Jumper bar assy. w/front wiring with base, cover and screw	1	QOU14100JBAF	
4P 100 A Jumper bar assy. w/right side wiring with base, cover and screw	1	QOU14100JBAR	
4P 100 A Jumper bar assy. w/left side wiring with base, cover and screw	1	QOU14100JBAL	
1Ø, 4P, 100 A Jumper bar base with front wiring	40	QOU14100BAFB	
1Ø, 4P, 100 A Jumper bar base with left side wiring	40	QOU14100BALB	
1Ø, 4P, 100 A Jumper bar base with right side wiring	40	QOU14100BARB	
4P Jumper bar cover	40	QOU14100CAB	
Mounting screw for jumper bar cover	40	QOU1CMSB	
6P 150 A Jumper bar assy. w/front wiring with base, cover and screw	1	QOU16150JBAF	
1Ø, 6P, 150 A Jumper bar base with front wiring	40	QOU16150BAFB	
1Ø, 6P, 150 A Jumper bar base with left side wiring	40	QOU16150BALB	
1Ø, 6P, 150 A Jumper bar base with right side wiring	40	QOU16150BARB	
6P jumper bar cover	40	QOU16150CAB	
Vertical rainproof cover 2P and 3P QO, QOU, FA and KA	1 10	BCVA♦♦ BCVB▲♦	
Horizontal rainproof cover 2P QO, QOU, and 3P Q2, EH	1 10	BCHA♦♦ BCHB▲♦	
1P Fingersafe™ cover for high ampere QOU circuit breaker	1 40	QOUHFSC1 QOUHFSC1B	
1P Fingersafe cover for low ampere QOU circuit breaker	1 40	QOULFSC1 QOULFSC1B	
Cover plate for one 2P QOU circuit breaker	1 40	QOUCP2 QOUCP2B	
Cover plate for one 3P QOU circuit breaker	1 40	QOUCP3 QOUCP3B	
Cover plate for two 2P QOU circuit breakers	1 40	QOUCP4 QOUCP4B	
Cover plate for three 2P QOU circuit breakers	1 40	QOUCP6 QOUCP6B	
Field-installable ring tongue terminal adaptor	1 80	QOVRT QOVRTB	
Quick connector end connection wiring	1 40	QOUEC QOUECB	
Quick connector forward or reverse wiring	1 40	QOUFR QOUFRB	
1P QOU mounting foot	1 80	QOUMF1▲ QOUMF1B▲	
2P QOU mounting foot	1 40	QOUMF2▲ QOUMF2B▲	
3P QOU mounting foot	1 24	QOUMF3▲ QOUMF3B▲	
Tapped mounting foot for QOU, 1P and 2P 10–70 A, 3P 10–60 A			
Packaged with circuit breaker		Suffix -3100	
Individually packaged	1	QOUMFS1	
Bulk packed	80	QOUMFS1B	
Mechanical interlock attachment: Used to interlock two circuit breakers mounted side-by-side so that only one circuit breaker can be ON at a time. A 1P or 2P circuit breaker can be mounted on the left and interlocked with a 2P or 3P circuit breaker on the right.	1	QOU2DTILA■	

- ▲ For use on low and high ampere QOU.
- 10–70 A 1P and 2P, 10–60 A 3P.
- ♦ DE2E Discount Schedule

**For QOUQ Low Ampere Circuit Breakers with Four-Point Quick-Connect Terminals**

QOUQ low ampere circuit breakers with four-point quick-connect terminals are provided with permanent factory-installed terminals which are affixed to the Load or OFF end of the circuit breaker. This special terminal will accommodate up to four 1/4-inch insulated female quick connect wire terminations. Total ampacity of these connections must not exceed the rating of the circuit breaker.

**Table 7.26: QOUQ Four-Point Quick-Connect Terminals**

	Poles	Order Qty.	Cat. No.	Unit \$ Price Adder
Four-Point Quick-Connect Terminals	1	1	Change QOU to QOUQ	_____
	2	1		_____
	3	1		_____

