

Main

Range	New Unica
Product or component type	Audio/video socket
Connector type	RCA
Electrical circuit type	Audio/video
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)
Type of packing	Flow-pack
Main colour tint	Anthracite

Complementary

Socket number	1
Fixing mode	Clip-in
Number of modules	1 module
Surface finish	Matt
Quantity per set	Set of 10
Connections - terminals	Screw terminals
Clamping connection capacity	<= 1.5 mm² for flexible cable(s) <= 1.5 mm² for rigid cable(s)
Wire stripping length	8 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PC (polycarbonate) GF10 FR: casing
Height	45 mm
Width	22.5 mm
Depth	28 mm
Embedding depth	19 mm
Net weight	0.02 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
IP degree of protection	IP2XC
IK degree of protection	IK02

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins