

Model No. 427

Labeled Snap-on Lockout Hasp, Red, 1-3/4in x 2-1/8in (44.5mm x 54mm) Jaw Clearance

Best Used For:

LOCKOUT/ TAGOUT Lockout Tagout

Overview & Features

Product Features

- Labeled Red Lockout Hasp
- Red lockout hasp with tagout identification for multiple workers
- Features an easy-to-apply andlsquo;snap-onandrsquo; advantage with its spring-loaded locking arm
- Fits more lockout points than alternative rivet-hinge labeled lockout hasps
- Anodized aluminum and stainless steel construction for combined corrosion-resistance and strength
- Complete with high visibility, write-on safety labels (English, French and Spanish)
- Dimensions are 2-7/8in x 7in (73mm x 178mm) with 1-3/4in x 2-1/8in (44mm x 54mm) inside jaw diameter, holds up to 5 safety padlocks

Product Details

The Master Lock No. 427 Labeled Red Safety Lockout Hasp features a 1-3/4in x 2-1/8in (45mm x 54mm) diameter inside jaw clearance and is designed to fit more lockout points than alternative rivet-hinge labeled lockout hasps. The anodized aluminum and stainless steel construction provides combined corrosion resistance and strength. A spring-loaded locking arm offers an easy-to-apply 'snap-on' advantage. Includes high-visibility, write-on safety labels to identify the responsible person.

Product Specifications

Product Number	427
Lockout Hasp Length	178 mm
Accepts Shackle Diameter up to	7 mm
Colour	Red
Description	Commercial Bagged
Shelf Pack Qty	6
Master Carton Qty	24

Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu