

111.16.050 16 bar G1/4B

Bourdon tube pressure gauges,model 111

Numéro d'article:	30698723	
Quantité:	1 pcs	
Code:	111.16-B-BG416Z-GB-BBZZNZ4Z-Z-ZZZZ DIAL-IAZ1ZZZZZZZZZ1Z- LABEL-E01DE-ZZZZZ	1SBZAAAZAC1 1Z1ZZ9ZZZZ
Vue d'ensemble:	111.16.050 16 bar G1/4B Connector location: center back mount Case: black plastic with front flange class 2.5 Window: plastic, clear Pointer: plastic, black standard packing Dial: plastic, white, with stop-pin stop-pin at zero *EN 837-1* *Cl.2.5* *WIKA*	
Détails:	Bourdon tube pressure gauges,model 111 Model: 111.16 Specifications according to data sheet Model: 111.16 panelmounting Nominal size: 050 mm Unit of outer Scale: bar Measuring range: gauge pressure range Scale range: 0...16 bar Process connection: G 1/4 B Connector location: center back mount Case: black plastic with front flange Window: plastic, clear Accuracy class: class 2.5 Overpressure safe: standard Ingress protection: Standard Pointer: plastic, black Packaging: standard packing Process connection surface area: brass Dial: plastic, white, with stop-pin Specifications according to data sheet: PM 01.10 Dial description: Pressure Gauge Standard: International (standard Europe) color for 1.scale (outside): black dial background: White Manufacturer logo: *WIKA* stop pin on dial: at zero	

Date: 06/04/2023



norm-mark on dial: *EN 837-1*
accuracy class on dial: *Cl.2.5*