



R-665

Premium leather work gloves with TPR impact protection, delivering advanced hand safety



Impact

Abrasion Protection



Cut



Medium Duty

Premium leather work gloves with TPR impact protection, delivering advanced hand safety

- **Specialized protection:** RINGERS® R665 safety gloves have been developed with F3 Technology™ and TPR impact protection at the knuckles, thumb and the full length of the fingers, for comprehensive personal protection
 - **Augmented dexterity:** These impact gloves are made from premium grain goatskin leather, ensuring comfort and dexterity, while protecting against impact hazards and cuts
 - **Advanced defenses:** These RINGERS® gloves include an extra palm layer for advanced cut protection, meeting ANSI/ISEA 105-2024 CUT A5 and EN ISO E standards
 - **Enhanced features:** Reinforced seams on the index finger and base of the thumb grant these impact gloves greater durability, while a hook and loop TPR pull tab wrist closure ensures a secure cuff
- *Not all sizes are available in all regions



Industries

- Manufacturing
- Oil and gas
- Machinery and Equipment
- Utilities

Applications

- Preparation of site - unloading of lines and valves
- Handling iron
- Handling of tools
- Operating of heavy machinery
- Equipment maintenance and repair
- Pipe handling
- Handling materials with sharp or rough edges
- Loading raw material



R-665

Premium leather work gloves with TPR impact protection, delivering advanced hand safety

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Goatskin leather:** Comfortable feel and heightened dexterity
- **Additional palm layer:** ANSI/ISEA and EN certified cut resistance

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



EN388: 2016



3X42EP

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	PACKAGE
RINGERS® R665	Liner Material: HPPE, Goatskin leather Cuff Style: Elastic cuff with hook and loop pull tab closure		8, 9, 10, 11, 12, 13	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

