

Transition sleeve from hose to cable - WP-EC TPE HF 10,0 BK - 3240974


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves, transition sleeves, from hose to cable



Key commercial data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710923
Weight per Piece (excluding packing)	1.5 g
Custom tariff number	39174000
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	29 mm
Inner diameter (f)	8.00 mm
Outside diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Short-term temperature	150 °C

General

Color	black
Components	Halogen-free
Inflammability class according to UL 94	HB
Material	TPE

Transition sleeve from hose to cable - WP-EC TPE HF 10,0 BK - 3240974

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27439210

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details

