



Microline Dot Matrix Printers

ML320 Elite ML321 Elite 9-Pin Dot Matrix Printer

A true representation of OKI Printing Solutions design philosophy and legendary build

The ML320/ML321 Elite narrow and wide carriage printers are suited to high speed, high volume data and word processing applications where speed is more important than letter quality. Reliability, ease-of-use and fast throughput make them ideal for customer service points in wholesale, retail and service environments.

Highlights:

- Versatile 80 column dot matrix printer
- OKI Printing Solutions unique, high durability 9-pin print head
- Up to 360 characters per second print speed
- Multi-part forms handling (original + 4 copies)
- Ideal for labels, listings and point of service applications
- Wide carriage ML321 (ideal for accounts applications) also available



ML320/ML321 ELITE

		ML320 Elite	ML321 Elite
General	Number of pins	9	
	No. of multi-part forms	5 (one original + 4 copies)	
Speed and throughput	Super speed (12cpi)	360cps	
	High speed draft (10cpi)	300cps	
	Utility (12cpi & 10cpi)	250cps	
	Near letter quality (12cpi & 10cpi)	63cps	
	Fastest print speed	360cps	
Font & print features	Carriage width (10cpi)	80 columns	136 columns
	Max. in compression mode	160 columns	272 columns
	Character pitch	10/12/15/17.1/20 pitch & proportional	
	Graphics resolution	Up to 240 x 216 dpi	
	Typeface & Font	NLQ-Courier, NLQ-Sans Serif, High Speed Draft, Utility	
	Typestyle	Emphasised, Enhanced, Double Width, Double Height, Italics, Bold, Superscript, Subscript, Underline, Overscore	
Emulations & Interfaces	Printer emulations	Epson FX, IBM Graphics/ProPrinter or Oki MicroLine	
	Standard interfaces	Centronics Parallel	
	Optional interfaces	Serial RS 232C/RS 422/Current Loop	
Paper handling	Continuous paper	76–254mm	76–406mm
	Continuous envelopes	165 x 91mm	239 x 102mm
	First printable line (from top of page)	Cut sheet: 23.4mm, Continuous: 23.4mm	
	Standard	Paper parking, Low tear-off, Push tractors, Autoload single sheet	
	Optional	Pull tractors, Single/dual bin sheet feeder	
Physical	Dimensions (HxWxD)	116 x 398 x 345mm	116 x 552 x 345mm
	Weight	7.8kg	10.1kg
	Memory	28KB	
	Noise level	57dB(A)/52dB(A) (quiet mode)	
Power	Power requirements	230V AC	
	Frequency	50/60Hz	
Reliability	Print head life	200 million characters	
	Ribbon life	3 million characters (re-inking cartridge)	
	MTBF	5,000 hours	

Consumables Information: Only use genuine OKI Printing Solutions Original consumables to ensure the best quality and performance from your hardware. Non OKI Printing Solutions Original products may damage your printer's performance and invalidate your warranty. Specifications subject to change without notice. All trademarks acknowledged.

