

STEP UP IN
COMFORT



COMFORT MEANS STANDING FIRM

VELOCITY IGS V1955

SPECIFICATION SHEET

W
Women's
Range

IGS
Intelligent
Grip System

Description

Built on a women's foot shape and featuring a lightweight nano composite toecap and protective midsole, this metal free trainer is incredibly comfortable and durable. Constructed from advanced materials, this leather free trainer is completely Vegan friendly. Now featuring the innovative IGS rubber sole ensuring superb grip on all surfaces and increased cushioning underfoot with a full length EVA midlayer. A further added benefit is they are fully ESD compliant.

Safety Specification

EN ISO 20345:2011 S1P HI HRO ESD SRC



Heat
Resistant



Anti-Static



Composite
Toecap



Composite
Midsole



Metal Free



Vegan
Friendly

Size

Available in sizes: UK 2 - 8 (EU 32 - 42)

Upper

Constructed from advanced materials, this leather free trainer is completely Vegan friendly.

Lining

Durable moisture wicking and highly breathable lining.

Insole

The dual comfort insole features unique airflow channels to maximise air circulation and reduce heat. With twin anti-shock foam pods the heel and the ball of the foot, this insole will provide daylong comfort where you need it most.

Toecap

Cutting edge, low profile, lightweight nano-composite non sparking and thermal insulating toecap. It has been tested to the impact of 200 Joules.

Protective midsole

Flexible woven composite material, pierce resistant to 1100N.

Sole

Inspired by tyre technology and made from highly durable rubber, the IGS sole unit features a unique hexagonal tread ensuring superior traction, ladder grips offering firefighter levels of safety and a re-designed heel strike pad delivering exceptional water dispersal.



The IGS is heat resistant to approximately 300°C. Non-marking and resistant to diesel, fat, acid and alkali.

Weight

512g

Warranty

We design our boots to the highest standard to ensure they keep you safe day after day. We're so confident that our boots will stand the test of time, that we offer a 200 day guarantee as standard.