

PREVOS1 SAFETY QUICK COUPLINGS - CSI 08

Bulkhead coupler

Profile : ISO 6150C



Part number	Female thread	Min. operating pressure (bar)	Flow rate at 6.00 bar (l/min) ($\Delta P = 0.60$ bar)	ID passage (mm)	Temperature min/max (°C)
CSI 082103	G1/2	2.00 / 12.00	2028.00	8 mm	-15.00 / 70.00

Part number	Dim. A (mm)	Dim. B (mm)	Dim. C (mm)	Dim. D (mm)
CSI 082103	82.00	32.00	29.00	32.00

