

DIN-Signal C064MS-3,0C1-1-NFF



Image is for illustration purposes only.
Please refer to product description.

Part number:	09 03 164 2921 222
Description:	DIN-Signal C064MS-3,0C1-1-NFF
No. of contacts:	64
Performance level:	PL 1 acc. to IEC 60603-2
pcb fixing:	without snap in clips
Quality-Level:	premium
usage on ...-side:	Daughtercard
Application:	VME
Contact Pitch:	2.54 mm
Series:	DIN 41612
Combination:	Backplane-to-Daughtercard ----- Extender Card ----- Cable to Board
Current:	2 A @ 20°C
contact orientation:	angled
Gender:	Male
Plastic features:	CTI < 400
Railway classification:	F1/I2 acc. to NFF 16-101
Type:	C
Termination Type:	Solder
Termination length:	3.0 mm
Flange:	with Flange
Mating face:	DIN type C/R
RoHS conformity:	Yes