

Han 10EMC/B-HCC2-HC-DL-M20-ML



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 810 0765 ML
Specification	Han 10EMC/B-HCC2-HC-DL-M20-ML
HARTING eCatalogue	https://harting.com/19628100765ML

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] EMC/B
Type of hood/housing	Cable to cable housing
Type	High construction

Version

Size	10 B
Version	Top entry
Number of cable entries	2
Cable entry	2x M20
Locking type	Double locking lever
Field of application	Hoods/Housings for higher EMC requirements

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

Material properties

Material (hood/housing)	Aluminium die-cast
-------------------------	--------------------



Pushing Performance
Since 1945

Material properties

Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
Material (locking)	Steel, zinc plated

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	1
Net weight	216 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140171763
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466