

Features

- 12 fibers optic pigtails
- Data processing networks
- Optical access network
- CATV, LAN, WAN, TEST

RS PRO Set Pigtail 9 G657.A1 900um Loose easy strip 12 Colors LC/UPC IL<0,25dB 2,00 m

RS Stock No.: 0794529



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

12 fibers optic pigtails are ideal for fusion splicing the required fiber connectivity for structured cabling systems including Data Centers, Broadband CATV, PON ,WDM or DWDM multiplexing, FTTH and voice services in ATM and SONET metropolitan and access networks. The OS2 bend insensitive fiber optic pigtails have less attenuation when bent or twisted compared with traditional fiber optic pigtails and this will make the installation and maintenance more efficient.

General Specifications

IL&RL TESTING	Compliant with IEC 61300-3-34
GEOMETRICAL CHARACTERISTICS	Compliant with IEC 61755-3-1
Connector End face	Compliant with IEC 61300-3-35

Technical Specifications

Connector Type	LC
Fiber	G657.A1
Cable	900um LSZH Loose Tube
Jacket Color	12 colors
Fiber Count	12 Fibers
Operating Temperature	20/70°C
Polish Type	UPC

Optical Specifications

Vibration	$\leq 0.2\text{dB}$
Insertion Loss	$\leq 0.3\text{dB}$
Return Loss	MM $\geq 30\text{dB}$ UPC $\geq 50\text{dB}$, APC $\geq 60\text{dB}$
Durability	1000 Times

Approvals

Declarations	MFR Declaration of Conformity
Standards Met	RoHS Compliant