

























Table 19.40: Heads for Ronis Key Operated Selector Switches ▲
(To combine with complete bodies and contact blocks, see page 19-7.)




Number and Type of Positions	Key Withdrawal	Rectangular	Square	Round	\$ Price
		Catalog Number			
Switching angle: maintained positions 70°, spring return positions 45°					
 ZB6DG•	 Right-hand position	ZB6DGA	ZB6CGA	ZB6AGA	45.60
	 Center position	ZB6DGB	ZB6CGB	ZB6AGB	
	 Both positions	ZB6DGC	ZB6CGC	ZB6AGC	
2-spring return from right to center	 Center position	ZB6DGL	ZB6CGL	ZB6AGL	
 ZB6CG•	 Left-hand position	ZB6DGD	ZB6CGD	ZB6AGD	
	 Center position	ZB6DGE	ZB6CGE	ZB6AGE	
	 Left-hand and center positions	ZB6DGF	ZB6CGF	ZB6AGF	
	 Right-hand position	ZB6DGG	ZB6CGG	ZB6AGG	
	 All 3 positions	ZB6DGH	ZB6CGH	ZB6AGH	
	 Left-hand and right-hand positions	ZB6DGJ	ZB6CGJ	ZB6AGJ	
	 Right-hand and center positions	ZB6DGK	ZB6CGK	ZB6AGK	
 ZB6AG•	 Right-hand position	ZB6DGM	ZB6CGM	ZB6AGM	
	 Center position	ZB6DGN	ZB6CGN	ZB6AGN	
	 Right-hand and center positions	ZB6DGP	ZB6CGP	ZB6AGP	
3-spring return from right to center	 Left-hand position	ZB6DGQ	ZB6CGQ	ZB6AGQ	
	 Center position	ZB6DGR	ZB6CGR	ZB6AGR	
	 Left-hand and center positions	ZB6DGS	ZB6CGS	ZB6AGS	
3-spring return to center	 Center position	ZB6DGT	ZB6CGT	ZB6AGT	

Note:  Indicates key withdrawal position.

▲ Ronis 200 key standard. Other keys available, refer to Catalog 9001CT0001.

Table 19.41: Selector Switch Sequence (using contact block assemblies, page 19-7)

2 Position Selector Switch			Contact block guide ■
			
O	X		1 N.O. (left or right)
X	O		1 N.C. (left or right)
O	X		1 N.O. and 1 N.C.
X	O		

3 Position Selector Switch			Contact block guide ■
			
O	O	X	1 N.O. (left)
X	O	X	2 N.O. wired in parallel (side by side)
X	O	O	1 N.O. (right)
O	X	X	1 N.C. (right)
X	X	O	1 N.C. (left)
O	X	O	2 N.C. wired in series (side by side)

■ As viewed from the front of the panel.

Legends..... pages 19-12 and 19-13

When ordering, please specify:

- Quantity
- Catalog Number