


FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Standard 1:1 FLK module, with spring-cage connection and flat-ribbon cable connector, no. of positions 40

Commercial data

Item number	2302942
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	DK2181
Catalog page	Page 302 (IF-2011)
GTIN	4017918941451
Weight per piece (including packing)	178.2 g
Weight per piece (excluding packing)	145.67 g
Customs tariff number	85369010
Country of origin	DE

FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	40
No. of channels	2
	4
	6
	8
	16
	32

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	$\leq 30 \text{ V AC}$
Operating voltage (DC)	$\leq 60 \text{ V DC}$
Current (per branch)	$\leq 1 \text{ A}$

Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 μs)

Supported controller ALLEN-BRADLEY SLC 500

Suitable I/O card	1746 OB 32
	1746 OV 32
	1746 IB 32
	1746 IV 32

Connection data

Connection 1 (control level)

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2 (field level)

Connection method	Spring-cage connection
Stripping length	7 mm

FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

Number of positions	40
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
	0.25 mm ² ... 2.5 mm ² (Ferrule without plastic sleeve)
	0.25 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 12
Pitch	5.08 mm

Signaling

Status display present	No
------------------------	----

Dimensions

Item dimensions

Width	112.5 mm
Height	77 mm
Depth	52.34 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM 40/ZFKDS - Termination board


2302942

<https://www.phoenixcontact.com/in/products/2302942>



Drawings

Circuit diagram



FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>


Accessories

FLK EZ-DR.../.../... - Cable

2295059

<https://www.phoenixcontact.com/in/products/2295059>

Round cable, with preassembly, not shielded, variable cable length



FLK 40/EZ-DR/ 50/KONFEK - Cable

2288985

<https://www.phoenixcontact.com/in/products/2288985>

Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 0.5 m



FLKM 40/ZFKDS - Termination board

2302942

<https://www.phoenixcontact.com/in/products/2302942>



FLK 40/EZ-DR/ 100/KONFEK - Cable

2288998

<https://www.phoenixcontact.com/in/products/2288998>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 1 m

FLK 40/EZ-DR/ 150/KONFEK - Cable

2289007

<https://www.phoenixcontact.com/in/products/2289007>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 1.5 m

FLKM 40/ZFKDS - Termination board

2302942

<https://www.phoenixcontact.com/in/products/2302942>



FLK 40/EZ-DR/ 200/KONFEK - Cable

2289010

<https://www.phoenixcontact.com/in/products/2289010>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 2 m

FLK 40/EZ-DR/ 250/KONFEK - Cable

2289023

<https://www.phoenixcontact.com/in/products/2289023>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 2.5 m

FLKM 40/ZFKDS - Termination board



2302942

<https://www.phoenixcontact.com/in/products/2302942>

FLK 40/EZ-DR/ 300/KONFEK - Cable

2289036

<https://www.phoenixcontact.com/in/products/2289036>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 3 m

FLK 40/EZ-DR/ 350/KONFEK - Cable

2289049

<https://www.phoenixcontact.com/in/products/2289049>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 3.5 m

FLKM 40/ZFKDS - Termination board

2302942

<https://www.phoenixcontact.com/in/products/2302942>



FLK 40/EZ-DR/ 400/KONFEK - Cable

2289052

<https://www.phoenixcontact.com/in/products/2289052>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 4 m

FLK 40/EZ-DR/ 600/KONFEK - Cable

2299589

<https://www.phoenixcontact.com/in/products/2299589>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 6 m

FLKM 40/ZFKDS - Termination board

2302942

<https://www.phoenixcontact.com/in/products/2302942>



FLK 40/EZ-DR/ 800/KONFEK - Cable

2299592

<https://www.phoenixcontact.com/in/products/2299592>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 8 m

FLK 40/EZ-DR/1000/KONFEK - Cable

2299602

<https://www.phoenixcontact.com/in/products/2299602>



Round cable set; connection 1: IDC/FLK socket strip (1x 40-position); connection 2: IDC/FLK socket strip (1x 40-position); cable length: 10 m

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in