

STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/in/products/3190632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module socket contact, inserted in the PCC or HCC plug housing after crimping the conductor, for 1.5 mm² ... 2.5 mm² conductors, ribbon contact

Commercial data

Item number	3190632
Packing unit	3,300 pc
Minimum order quantity	3,300 pc
Sales key	ACE
Product key	AACCEG
Catalog page	Page 439 (C-3-2013)
GTIN	4017918100568
Weight per piece (including packing)	0.95 g
Weight per piece (excluding packing)	0.95 g
Customs tariff number	85366990
Country of origin	CZ

STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/in/products/3190632>

Technical data

Product properties

Product type	Connector
Product family	Metal
Pitch	0 mm

Electrical properties

Nominal current I_N	10 A
-----------------------	------

Dimensions

Pitch	0 mm
-------	------

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface contact area (top layer)	Tin Sn)

Standards and regulations

Connection in acc. with standard	EN-VDE
----------------------------------	--------

STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/in/products/3190632>

Classifications

ECLASS

ECLASS-11.0	27469090
ECLASS-13.0	27469090
ECLASS-12.0	27469090

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STG-MTN 1,5-2,5 BAND - Crimp contact



3190632

<https://www.phoenixcontact.com/in/products/3190632>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

STG-MTN 1,5-2,5 BAND - Crimp contact



3190632


<https://www.phoenixcontact.com/in/products/3190632>

Mandatory accessories

PCC 4/ 2-ST-7,62 - PCB connector

1840191

<https://www.phoenixcontact.com/in/products/1840191>




PCB connector, nominal cross section: 4 mm², color: green, nominal current: 20 A, rated voltage (III/2): 1000 V, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: PCC 4/..-ST, pitch: 7.62 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON PC 4, locking: without, mounting method: without, type of packaging: packed in cardboard, Corresponding female crimp contacts with current [A] and conductor cross section range [mm²] data: 13,5A/STG-MTN 0,5-1,0 (3190438); 13,5A/STG-MTN 0,5-1,0 BA (3190629); 20A/STG-MTN 1,5-2,5 (3190506); 20A/STG-MTN 1,5-2,5 BA (3190632). BA = Taped contacts

Accessories

PCC 4/ 2-ST-7,62 - PCB connector

1840191

<https://www.phoenixcontact.com/in/products/1840191>



PCB connector, nominal cross section: 4 mm², color: green, nominal current: 20 A, rated voltage (III/2): 1000 V, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: PCC 4/..-ST, pitch: 7.62 mm, connection method: Crimp connection, conductor/PCB connection direction: 0 °, locking clip: - Locking clip, plug-in system: COMBICON PC 4, locking: without, mounting method: without, type of packaging: packed in cardboard, Corresponding female crimp contacts with current [A] and conductor cross section range [mm²] data: 13,5A/STG-MTN 0,5-1,0 (3190438); 13,5A/STG-MTN 0,5-1,0 BA (3190629); 20A/STG-MTN 1,5-2,5 (3190506); 20A/STG-MTN 1,5-2,5 BA (3190632). BA = Taped contacts

STG-MTN 1,5-2,5 BAND - Crimp contact

3190632


<https://www.phoenixcontact.com/in/products/3190632>



CEC 2,5 - Filler plug

3062757

<https://www.phoenixcontact.com/in/products/3062757>



Cover for conductor shaft, 10-pos., for spring cage terminal blocks (ST) and terminal blocks with push-in technology (PT) with a width of 5.2 mm

WST 2,5 - Warning cover

3030941

<https://www.phoenixcontact.com/in/products/3030941>



Warning cover, 5-pos., for terminal width: 5.2 mm

STG-MTN 1,5-2,5 BAND - Crimp contact

3190632

<https://www.phoenixcontact.com/in/products/3190632>



STG-EW - Contact removal tool

3190441

<https://www.phoenixcontact.com/in/products/3190441>



Contact removal tool

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in