

HM 2620 E

EAN 4007841 089528
Article number 089528

series 7

2300 W

2300 W Output

Display

Display (LCD)



50 - 700°C



stepless adjustable



150 - 500 l/Min.

Suitable for screwable
nozzles

CE



VDE

Function description

Power and advanced technology, the HeatMatic 2620 E hot air gun offers maximum precision for professional applications and is also lightweight, ergonomic and absolutely robust.

Technical specifications

Temperature	50 – 700 °C	Function, hanger	No
Airflow rate	150 – 500 l/min	Restart protection	Yes
Temperature setting	in 10°C steps by joystick	Dimensions (L x W x H)	358 x 91 x 95 mm
Settings made via	joystick	PU1, net weight	1,16 kg
Temperature display	LCD display	Manufacturer's Warranty	1 year
Residual heat indicator	Yes	PU1, EAN	4007841089528
Heating element	Ceramic heating element	Output	2300 W
Mains power supply	220 – 230 V / 50 – 60 Hz	Product category	Hot air tool

Accessories

EAN 4007841 011871	Soldering reflector nozzle
EAN 4007841 007812	Flat angled nozzle 20x2 mm, 100°
EAN 4007841 011857	Reflector nozzle 20mm
EAN 4007841 092214	Round nozzle Ø 5 mm
EAN 4007841 009076	Round nozzle Ø 5 mm, extended
EAN 4007841 092313	Round nozzle Ø 10 mm
EAN 4007841 010409	Sieve reflector nozzle 50 x 35 mm

HM 2620 E

EAN 4007841 089528
Article number 089528



Accessories

EAN 4007841 011765	Fast welding nozzle 4mm narrow - for 5mm rd. noz.
EAN 4007841 011840	Fast welding nozzle 5mm narrow - for 5mm rd. noz.
EAN 4007841 010287	Fast welding nozzle 5mm - for 10mm rd. noz.
EAN 4007841 006785	Pressure roller Silicone Ø 35 mm 40 mm
EAN 4007841 084967	Pressure roller Silicone Ø 35 mm 28 mm
EAN 4007841 034115	Pressure roller 7mm - Brass
EAN 4007841 093211	Pressure roller 50mm - Rubber
EAN 4007841 034122	Pressure roller 40mm - Teflon
EAN 4007841 094317	Flat nozzle 60x2 mm for bitumen 60x2 mm
EAN 4007841 094287	Angled flat nozzle 20x2 mm - angled
EAN 4007841 094300	Angled flat nozzle 40x2 mm perforated
EAN 4007841 094294	Angled flat nozzle 40x2 mm