

# 4 Port DisplayPort KVM Switch with 4K 60Hz Resolution

Product ID: SV431DPUA2



This 4-port KVM switch combines 4K (60Hz) digital display capabilities with control of up to four connected computers.

## 4K60 Picture and Full Audio Support

The DisplayPort KVM switch supports resolutions up to 4K at 60Hz and can drive one large DP display with ease, maximizing viewing space. With support for 7.1 HD digital audio (with supporting displays and sources) and separate 3.5 mm stereo audio, the DisplayPort 1.2 KVM switch delivers full audio compatibility.

## Integrated USB Hub

The integrated USB 2.0 hub shares two additional peripherals (in addition to keyboard and mouse) among attached computers as if they were directly connected, eliminating the cost of duplicate devices such as printers and scanners.

## **PC and Mac Compatible**

While supporting PCs, this DP KVM switch is also compatible with Mac computers using a Mini DisplayPort adapter, including laptops, notebooks, and tablets.

## **Simple to Operate**

The front-panel pushbuttons make it easy to switch between systems and activate the auto scan. The hotkey functionality makes accessing each system quick while a buzzer sound confirms the switch.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors. This USB KVM switch is backed by a 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- High-res medical imaging
- High-res digital signage server control
- Multimedia design and production

### Features

- TAA compliant for government GSA schedule purchases
- Increases productivity with ports to connect up to 4 HD multimedia computers
- Achieves high picture quality with 4K resolutions @ 60Hz
- Eliminates the need to purchase extra equipment with built-in 2-port USB 2.0 hub
- Ensures full audio compatibility with 7.1 HD digital and separate 3.5 mm audio support

<b>Hardware</b>	Warranty	3 Years	
	Audio	Yes	
	Cables Included	No	
	Daisy-Chain	No	
	KVM Ports	4	
	Number of Monitors Supported	1	
	PC Interface	USB	
	PC Video Type	DisplayPort	
	Rack-Mountable	Optional	
	U Height	1U	
<b>Performance</b>	Auto Scan	3, 8, 15 & 30 seconds	
	Hot-Key Selection	Yes	
	IP Control	No	
	Maximum Data Transfer Rate	480 Mbps (USB 2.0)	
	Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz	
	Maximum Number of Users	1	
	MTBF	138327 hours	
	On-Screen Display	No	
	Port Selection Support	Push Button and Hotkeys	
	Wide Screen Supported	Yes	
<b>Connector(s)</b>	Console Interface(s)	1 - DisplayPort (20 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female 2 - USB Type-A (4 pin; HID Port) USB 1.1 Female	
	Host Connectors	4 - DisplayPort (20 pin) Female 4 - USB B (4 pin) Female 8 - 3.5 mm Mini-Jack (3 Position) Female	
<b>Software</b>	OS Compatibility	OS independent: No software or drivers required	
<b>Indicators</b>	LED Indicators	1 - Power 4 - Green - Online indicator (One LED per port) 4 - Red - Select indicator (One LED per port)	
	<b>Power</b>	Center Tip Polarity	Positive

	Input Current	0.6 A
	Input Voltage	100 ~ 240 AC
	Output Current	1.5 A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	18 W
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0% ~ 40%
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 60°C (14°F to 140°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel
	Product Height	1.8 in [45 mm]
	Product Length	8.7 in [220 mm]
	Product Weight	36.8 oz [1042 g]
	Product Width	5.2 in [131 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	3.5 lb [1.6 kg]
<b>What's in the Box</b>	Included in Package	1 - KVM switch
		4 - foot pads
		1 - universal power adapter (NA/JP, EU, UK, ANZ)
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.