

910.11 SS G1/2B / G1/2 union nut DIN 16271

DIN-Shut-off valve

Item number: 9095144

Quantity: 1 pcs.

Order code: 910.11-SS21CB-1ZZ-P32-ZZ 0

Overview: 910.11 SS G1/2B / G1/2 union nut DIN 16271

DIN-Shut-off valve

Material body: Stainless steel 1.4571

Version: with test connection, per DIN 16271 or similiar (with vent screw)

Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut

Design: Form B, with nipple and union nut as well as shaft for mounting bracket

Test connection: M20 x 1,5

Material packing: PTFE

Permissible medium temperature: -40...+200°C

Nominal pressure: PN max. 400 bar

Details:

DIN-Shut-off valve

Specifications according to data sheet: AC 09.02

Version: with test connection, per DIN 16271 or similiar (with vent screw)

Material body: Stainless steel 1.4571

Material packing: PTFE

Permissible medium temperature: -40...+200°C

Nominal pressure: PN max. 400 bar

Design: Form B, with nipple and union nut as well as shaft for mounting bracket

Connection process side + instrument side: G 1/2 B male + G 1/2 with nipple and union nut

Test connection: M20 x 1,5