
## **KEMET Part Number: SH-102**

(UDLSH001020000)



## KEMET, SH, DC Line Filters, Common Mode, 1500 nH



Dimensions		
L	12.5mm MAX	
W	10mm MAX	
Н	12mm MAX	
LL	4mm +/-1mm	
S	10mm +/-0.5mm	

Packaging Specifications		
Packaging:	Bulk, Box	
Packaging Quantity:	3000	
Weight:	1.67 g	

General Information		
Series:	SH	
Style:	Through-Hole	
RoHS:	Yes	
Miscellaneous:	For 2 Lines	

Specifications		
Voltage DC:	150 VDC	
Inductance:	1.5 uH	
Temperature Range:	-25/+80°C	
DC Resistance:	26 mOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

