



NO	DESCRIPTION	DATE
△	ADD M/S PART NO	04.01.04
△	ADD DESCRIPTION ADD 6.2±0.38	
	47.04±0.13 — 47.04±0.25	
	38.38±0.13 — 38.38±0.25	
	#3.05 — #3.05±0.25	
	7.9 — 7.9±0.25	
△	12.55 REF. — 12.55±0.38	03.13.08
	2.77 — 2.77±0.38	
	41.3 REF. — 41.28±0.38	
	1 — 0.76±0.25	
	10.72 REF. — 10.72±0.38	
	11 REF. — 10.72±0.38	
	3.3 REF. — 2.8±0.7	
	2.84 — 2.84±0.38	
	M/S PART NO. — P/N	
△	CORRECT DIMENSION LINE POSITION	12.02.11

CONTACT TYPE FORMED CONTACT
 COLOR OF INSULATION WHITE PBT GLASSFIBRE REINFORCED
 PLATING OF CONTACT GOLD <5 MICRO INCHES>
 SOLDER TERMINATIONS TIN
 WORKING VOLTAGE 500V AC AT SEA LEVEL
 CONTACT RESISTANCE 10m OHM MAX.
 MATING CYCLES 150 TIMES



△△ P/N: 544-3828

APPROVED by _____ DATE: _____



DESCRIPTION		D-SUB WITH 25-PIN FEMALE CONNECTOR BY FORMING						
製圖	DRAWN	TOLERANCE	品名	050-0025S-F	日期	DATE	版次	REV.
	Gina	.X ±0.2	TITLE	\ROHS COMPLIANT	02.23.95		A-3	
檢圖	CHECK	.XX ±0.1	單位	mm(in)	DWG.NO. 55-0052			
	Jase	.XXX ±0.05	比例	SCALE				
認定	APPROVAL	ANGLE ±5°						
	Angela							